## LASER®

## **Extractor - AdBlue® 1.5L**

This 1.5 litre capacity syringe is manufactured from materials specifically chosen to work with urea based solutions like AdBlue<sup>®</sup>. Fitted with a shut off valve and extension pipe to allow safe transfer of AdBlue® from commercially available containers into a vehicle as well as to draw off AdBlue® from the vehicles tank where over fill is suspected. N.B: some motor manufacturers recommend that an air gap be left in the vehicle tank to ensure room for expansion and proper aeration of the fluids.



## **Additional Information**

- 1.5L capacity to help prevent over filling of the AdBlue® tank.
- Twist and turn shut off valve to help prevent spillage during fluid transfer.
- 410mm long delivery/extraction pipe.
- Removable ends allow for easy cleaning.
- WARNING: Never put AdBlue® or other aqueous urea solutions into the main fuel tank. Such solutions are only used where a vehicle is fitted with SCR (Selective Catalytic Reduction) systems requiring the use of AdBlue® and equipped with a separate AdBlue® tank.

http://lasertools.co.uk/product/6153

Video available: http://youtu.be/mnn57j7BOy4

LASER Kamasa Gunson Onnec







LASER Kamasa Gunson Onnect Prec

26 Apr 2024